Waverunner-2 Oscilloscopes Specifications

Vertical System Input Channels	LT374 / M / L	LT372	LT264/M 4	LT262	
Analog Bandwidth @ 50 Ω (-3 dB)	500 MHz	500 MHz	350 MHZ	350 MHz	
Hardware Bandwidth Limits	20 MHz or 200 MHz				
nput Impedance	$50 \Omega \pm 1\%$; 10 M Ω /12 pF typical (using PP006 probe)				
nput Coupling	1 MΩ: AC, DC, GND; 50 Ω: DC, GND				
Maximum Input	50 Ω : 5 Vrms; 1 M Ω : 400 Vrmax (peak AC \leq 5 kHz + DC)				
/ertical Resolution	8 bits; up to 11 bits with enhanced resolution (ERES)				
Sensitivity (50 Ω or 1 M Ω)	2 mV - 10 V/div fully variable				
DC Gain Accuracy	± (1.5% + 0.5% of full scale)				
Offset Accuracy (50 Ω or 1 M Ω)	± (1.5% + 0.5% of full scale + 1 mV)				
Offset Range				**	
	2 mV – 99 mV/div:±1 V				
		100 mV - 99 V/div: ±10			
		1 V - 10 V/div:±100 V			
solation — Channel to Channel		>250:1 at same V/div sett	tings		
Timebase System			3		
Timebases		lain and up to four independent zoom t	traces simultaneously		
Ranges	500 ps/div - 1		1 ns/div –	1000 s/div	
Clock Accuracy		≤10 ppm		· · · · · · · · · · · · · · · · · · ·	
nterpolator Resolution	5 ps				
xternal Clock Frequency	500 MHz maximum, 50 Ω , or 1 M Ω impedance				
Roll Mode - Operating Range	time/div 500 ms – 1000 s/div or sample rate <100 kS/s max				
external Timebase Clock	500 MF	Hz maximum external sample clock inpu	ut on front panel EXT BNC		
Acquisition System Single Shot Sample Rate					
1 Channel Max.	4 GS/s	4 GS/s	1 GS/s	1 GS/s	
2 Channels Max.	4 GS/s	2 GS/s	1 GS/s	1 GS/s	
3 – 4 Channels Max.	2 GS/s	NA	1 GS/s	NA	
Maximum Acquisition Points/Ch					
Maximum Acquisition Points/Ch 1 Channel Max.	500k/2M/8M	500k	100k/1 M	100k	
	500k/2M/8M 500k/2M/8M	500k 250k	100k/1 M 100k/1 M	100k 100k	
	500k/2M/8M 500k/2M/8M 250k/1M/4M			1.7.7.1	
1 Channel Max. 2 Channels Max. 3 – 4 Channels Max. Acquisition Modes	500k/2M/8M	250k NA 50 GS/s for repetitive signals: 500 p	100k/1 M 100k/1 M os/div – 1 µs/div	100k	
1 Channel Max. 2 Channels Max. 3 – 4 Channels Max. Acquisition Modes Random Interleaved Sampling (RIS)	500k/2M/8M	250k NA	100k/1 M 100k/1 M os/div – 1 µs/div	100k	
1 Channel Max. 2 Channels Max. 3 – 4 Channels Max. Acquisition Modes Random Interleaved Sampling (RIS) Single Shot Sequence	500k/2M/8M	250k NA 50 GS/s for repetitive signals: 500 p	100k/1 M 100k/1 M os/div – 1 µs/div	100k	
1 Channel Max. 2 Channels Max. 3 – 4 Channels Max. Acquisition Modes Random Interleaved Sampling (RIS) Single Shot	500k/2M/8M	250k NA 50 GS/s for repetitive signals: 500 p	100k/1 M 100k/1 M os/div – 1 µs/div	100k	
1 Channel Max. 2 Channels Max. 3 – 4 Channels Max. Acquisition Modes Random Interleaved Sampling (RIS) Gringle Shot Grequence	500k/2M/8M	250k NA 50 GS/s for repetitive signals: 500 p For transient and repetitive signals: 1 n	100k/1 M 100k/1 M os/div – 1 µs/div	100k	
1 Channel Max. 2 Channels Max. 3 – 4 Channels Max. Acquisition Modes Random Interleaved Sampling (RIS) Single Shot Sequence LT262/264	500k/2M/8M	250k NA 50 GS/s for repetitive signals: 500 p For transient and repetitive signals: 1 n 2 – 400 segments	100k/1 M 100k/1 M os/div – 1 µs/div	100k	
1 Channel Max. 2 Channels Max. 3 – 4 Channels Max. Acquisition Modes Random Interleaved Sampling (RIS) Single Shot Sequence LT262/264 LT372/374	500k/2M/8M	250k NA 50 GS/s for repetitive signals: 500 p. For transient and repetitive signals: 1 n 2 – 400 segments 2 – 1 000 segments	100k/1 M 100k/1 M os/div – 1 µs/div	100k	
1 Channel Max. 2 Channels Max. 3 – 4 Channels Max. Acquisition Modes Random Interleaved Sampling (RIS) Single Shot Sequence LT262/264 LT372/374 Memory Option M or L	500k / 2M / 8M 250k / 1M / 4M Summed averaging to 10	250k NA 50 GS/s for repetitive signals: 500 p For transient and repetitive signals: 1 n 2 - 400 segments 2 - 1 000 segments 2 - 4 000 segments 50 µsec max.	100k / 1 M 100k / 1 M ps/div – 1 µs/div ns/div – 1000 s/div veighting range from 1:1 to 1:102	100k NA	
1 Channel Max. 2 Channels Max. 3 – 4 Channels Max. Acquisition Modes Random Interleaved Sampling (RIS) Single Shot Sequence LT262/264 LT372/374 Memory Option M or L Intersegment Time Acquisition Processing	500k / 2M / 8M 250k / 1M / 4M Summed averaging to 10	250k NA 50 GS/s for repetitive signals: 500 p For transient and repetitive signals: 1 n 2 – 400 segments 2 – 1 000 segments 2 - 4 000 segments 50 µsec max.	100k / 1 M 100k / 1 M 100k / 1 M ps/div – 1 µs/div ns/div – 1000 s/div reighting range from 1:1 to 1:102 optional with WAVA)	100k NA	

Triggering System		
Modes	Normal, Auto, Single, and Stop	
Sources	Any input channel, external, Ext/10 or line; slope, level, and coupling unique to each source (except line trigger)	
Sources	Inactive channels usable as trigger inputs.	
Slope	Positive, Negative, Window	
Coupling modes	DC, AC, HFREJ, LFREJ	
AC Cutoff Frequency	7.5 Hz Typical	
HFREJ, LFREJ	50 kHz typical	
Pre-trigger delay	0 – 100% of horizontal time scale	
Post-trigger delay	0 – 10 000 divisions	
Hold-off by time or events	Up to 20s or from 1 to 99 999 999 events	
Internal trigger range	±5 div	
Max trigger frequency	500 MHz (350MHz on LT264, LT262)	
External trigger input range	± 0.5 (± 5 V with Ext/10 selected)	
Maximum ext. input @ 50 Ω	±5 V DC or 5Vrms	
Maximum ext. input @ 1 MΩ	400 Vmax (DC + peak AC < 5 kHz)	
Automatic Setup		
Auto Setup	Automatically costs timehase trigger and consist in the display a wide space of constitution of the	
Vertical Find	Automatically sets timebase, trigger, and sensitivity to display a wide range of repetitive signals Automatically sets the vertical sensitivity and offset for the selected channels to display a waveform with maximum dynamic range	
vertical fillio	Automatically sets the vertical sensitivity and offset for the selected channels to display a waveform with maximum dynamic range	
Probes		
Model PP006	$10:1,10 \mathrm{M}\Omega$ with auto-detect (one per channel)	
Probe System: ProBus	Automatically detects and supports a wide variety of differential amplifiers; active, high-voltage, current, and differential probes	
Scale Factors	Up to 12 automatically or manually selected	
Color Waveform Display		
Туре	VGA color 8.4" flat-panel TFT-LCD	
Resolution	VGA 640 x 480 pixels	
Screen Saver	Display blanks after 10 minutes (when screen saver is "on")	
Real Time Clock	Date, hours, minutes, and seconds displayed with waveform	
Number of Traces	Display a maximum of eight traces. Simultaneously display channel, zoom, memory, and math traces.	
Grid Styles	Single, Dual, Quad, Octal, XY, Single + XY, Dual + XY; Full Screen gives enlarged view of each style.	
Intensity Controls	Separate intensity control for grids and waveforms	
Waveform Styles	Sample dots joined or dots only — regular or bold sample point highlighting	
Trace Overlap Display	Select opaque or transparent mode with automatic waveform overlap management.	
Analog Persistence Display		
	Markle as well as the state of	
Analog & Color-Graded Persistence Trace Selection	Variable saturation levels; stores each trace's persistence data in memory	
Persistence Aging Time	Activate Analog Persistence on a selected trace, top 2 traces, or all traces Select from 500 ms to infinite	
Trace Display Sweeps Displayed	Opaque or transparent overlap All accumulated or all accumulated with last trace highlighted	
	The decent disters of an account disters that the ring may need	
Zoom Expansion Traces		
Display up to Four Zoom Traces		
Vertical Zoom	Up to 5X expansion, 50X with averaging	
Horizontal Zoom	Expand to 2 pts/div, magnify to 50 000X	
Auto Scroll	Automatically scan and display any zoom or math trace.	
Rapid Signal Processing		
Processor	Power PC	
Processing Memory	Up to 128 Mbytes	
Realtime Clock	Dates, hours, minutes, seconds, and time stamp trigger time to 1 ns resolution	

Waverunner-2 Oscilloscopes Specifications, Continued

Internal Waveform Memory		
Waveform	M1, M2, M3, M4 (Store full-length waveforms with 16 bits/data point)	
Zoom and Math	Four traces A, B, C, D with chained trace capability	
Setup Storage		
Front Panel and Instrument Status	Four non-volatile memories and floppy drive are standard. Hard drive and memory card are optional.	
Interface		
Remote Control	Full control of all front panel controls and internal functions via RS232C, GPIB, or Ethernet (optional)	
RS-232-C	Asynchronous transfer rate of up to 115.2 kbaud	
GPIB Port	Full control via IEEE – 4888.2; configurable as talker/listener for computer control and data transfer	
Ethernet (optional)	10 Base-T Ethernet interface	
Floppy Drive	Internal, DOS-format, 3.5" high-density	
PC Card Slot (optional)	Supports memory and hard drive cards	
External Monitor Port Standard	15-pin D-Type VGA-compatible	
Centronics Port	Parallel printer interface	
Internal Graphics Printer (optional)	Provides hard copy output in <10 seconds	
Outputs		
Calibrator Signal	500 Hz – 1 MHz square wave or DC level; Select from -1.0 to +1.0 into 1 M ohm, output on front panel test point and ground lug.	
Control Signals	Rear Panel, TTL level, BNC output; Choice of trigger ready, trigger out, pass/fail status. (output resistance $300\Omega \pm 10\%$)	
Environmental and Safety		
Secretaria de la composición del la composición del composición de la composición del composición del composición de la composición de la composición del composic		
Operating Conditions	5 40 °C 4 1 1 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2	
Temperature	5 – 40 °C rated accuracy	
	0 – 45 °C operating -20 – 60 °C non-operating	
[]	80% max RH, non-condensing up to 35 °C; Derates to 50% max RH, non-condensing at 45 °C	
Humidity	4 500 m (15 000 ft) max. up to 25 °C; Derates to 2 000 m (6 600 ft) at 45 °C	
Altitude	4 500 fm (15 000 ft) fmax. up to 25 °C, Defates to 2 000 fm (0 000 ft) at 45 °C	
CE Approved EMC	EMC Directive 89/336/EEC; EN 61326-1 Emissions and Immunity	
	Low Voltage Directive 73/23/EEC; EN 61010-1 Product Safety (Installation Category II, Pollution Degree 2)	
Safety UL and cUL approved	UL Standard UL 3111-1	
or and cor approved	cUL Standard CSA C22.2 No. 1010-1	
General		
Auto Calibration	Ensures specified DC and timing accuracy is maintained for 1 year minimum	
Auto Calibration time	< 500 ms	
Power Requirements	90 – 132 VAC at 45 - 440 Hz	
1 Office haddinethalia	180 - 250 VAC at 45 - 66 Hz	
	Automatic AC voltage selection	
	Power Consumption: 150 – 230 VA depending on model	
Battery Backup	Front panel settings retained for two years minimum	
Warranty and Calibration	Three years; calibration recommended yearly	
Physical Dimensions		
Dimensions (HWD)	210 mm x 350 mm x 300 mm; 8.3" x 13.8" x 11.8" (height excludes feet)	
Weight	18 lbs (8 kg)	
Shipping Weight	27 lbs (12 kg)	
Shipping weight	21 IND (12 INS)	