

Specifications

This section lists the electrical, environmental, and physical specifications of the YOPM100 and 200 Optical Power Meters. All specifications are guaranteed unless labeled “typical”. Typical specifications are provided for your convenience and are not guaranteed.

The specifications in this section apply to the YOPM modules, unless otherwise specified. For NetTek Analyzer Platform specifications, refer to the NetTek Analyzer Platform User Manual.

Table 7: NetTek Analyzer YOPM module characteristics

Module	Range	Wavelengths	Power range
YOPM100	Standard	850, 980, 1300, 1310, 1480, 1550, 1625nm	+3 dBm to -65 dBm
YOPM200	Extended	980, 1300, 1310, 1480, 1550, 1625nm	+27 dBm to -43 dBm ¹

1 Limit exposure to high power (greater than +23 dBm) to less than 2 minutes. Follow high-power exposure by a cool-off time at least 15 times the exposure time.

Table 8: Physical characteristics

Module	Power range
Dimensions of the test head	Height: 135 mm (4.4 in) Width: 61 mm (2.4 in) Depth: 26 mm (1.0 in)
Weight	<0.18 kg (<0.4 lbs.)

Table 9: General characteristics

Characteristic	Description
Accuracy ¹	
980, 1300, 1310, 1480, & 1550 nm	±0.25 dB at calibration conditions, NIST Traceable
850, 1625 nm	±0.32 dB at calibration conditions, typical
Resolution of real-time display	0.01 or 0.1 (selectable)
Platform	
Hardware	Tektronix NetTek Y350 platform
Software	Windows CE version 2.13 and above
Number of stored tests	1152 tests (48 x 24 table)

¹ **Within specified ambient environment of 23° C.**

Table 10: Environmental characteristics

Characteristic	Description
Temperature Range	
Operating	-10° C to +50° C
Nonoperating	-40° C to +60° C
Humidity, operating	5% to 95% RH
Altitude	
Operating	Up to 4.6 km (15,000 ft.)
Nonoperating	Up to 15.24 km (50,000 ft.)

Table 11: Certifications and compliances

Category	Standards or description																
EC Declaration of Conformity - EMC	<p>Meets intent of Directive 89/336/EEC for Electromagnetic Compatibility. Compliance was demonstrated to the following specifications as listed in the Official Journal of the European Communities:</p> <table border="0"> <tr> <td data-bbox="617 619 893 766">EN 61326</td> <td data-bbox="893 619 1393 766">EMC requirements for Class A electrical equipment for measurement, control and laboratory use.</td> </tr> <tr> <td data-bbox="617 787 893 871">IEC 61000-4-2</td> <td data-bbox="893 787 1393 871">Electrostatic discharge immunity (Performance criterion B)</td> </tr> <tr> <td data-bbox="617 892 893 976">IEC 61000-4-3</td> <td data-bbox="893 892 1393 976">RF electromagnetic field immunity (Performance criterion A)</td> </tr> <tr> <td data-bbox="617 997 893 1081">IEC 61000-4-4</td> <td data-bbox="893 997 1393 1081">Electrical fast transient / burst immunity (Performance criterion B)</td> </tr> <tr> <td data-bbox="617 1102 893 1186">IEC 61000-4-5</td> <td data-bbox="893 1102 1393 1186">Power line surge immunity (Performance criterion B)</td> </tr> <tr> <td data-bbox="617 1207 893 1291">IEC 61000-4-6</td> <td data-bbox="893 1207 1393 1291">Conducted RF immunity (Performance criterion A)</td> </tr> <tr> <td data-bbox="617 1312 893 1396">IEC 61000-4-11</td> <td data-bbox="893 1312 1393 1396">Voltage dips and interruptions immunity (Performance criterion B)</td> </tr> <tr> <td data-bbox="617 1417 893 1428">EN 61000-3-2</td> <td data-bbox="893 1417 1393 1428">AC power line harmonic emissions</td> </tr> </table>	EN 61326	EMC requirements for Class A electrical equipment for measurement, control and laboratory use.	IEC 61000-4-2	Electrostatic discharge immunity (Performance criterion B)	IEC 61000-4-3	RF electromagnetic field immunity (Performance criterion A)	IEC 61000-4-4	Electrical fast transient / burst immunity (Performance criterion B)	IEC 61000-4-5	Power line surge immunity (Performance criterion B)	IEC 61000-4-6	Conducted RF immunity (Performance criterion A)	IEC 61000-4-11	Voltage dips and interruptions immunity (Performance criterion B)	EN 61000-3-2	AC power line harmonic emissions
EN 61326	EMC requirements for Class A electrical equipment for measurement, control and laboratory use.																
IEC 61000-4-2	Electrostatic discharge immunity (Performance criterion B)																
IEC 61000-4-3	RF electromagnetic field immunity (Performance criterion A)																
IEC 61000-4-4	Electrical fast transient / burst immunity (Performance criterion B)																
IEC 61000-4-5	Power line surge immunity (Performance criterion B)																
IEC 61000-4-6	Conducted RF immunity (Performance criterion A)																
IEC 61000-4-11	Voltage dips and interruptions immunity (Performance criterion B)																
EN 61000-3-2	AC power line harmonic emissions																
Australia / New Zealand Declaration of Conformity - EMC	<p>Complies with EMC provision of Radiocommunications Act per the following standard(s):</p> <table border="0"> <tr> <td data-bbox="617 1533 893 1606">AS/NZS 2064.1/2</td> <td data-bbox="893 1533 1393 1606">Industrial, Scientific, and Medical Equipment: 1992</td> </tr> </table>	AS/NZS 2064.1/2	Industrial, Scientific, and Medical Equipment: 1992														
AS/NZS 2064.1/2	Industrial, Scientific, and Medical Equipment: 1992																
FCC	Emissions comply with FCC Code of Federal Regulations 47, Part 15, Subpart B, Class A Limits.																

Options, Accessories, and Replaceable Parts

The tables below list part numbers of options and accessories that you can order for your power meter. Contact your Tektronix representative or distributor for ordering information. See page vii for information on contacting Tektronix.

Table 12: SOC connector part numbers

Description	Part number
FC	119-5146-00
E2000	119-5165-00
ST	119-5144-00
Diamond 3.5	119-5172-00
SC	119-5145-00

Table 13: Standard accessories

Quantity	Part number	Description
1 ea	020-2357-00	Cleaning kit
1 ea	020-2414-00	English user manual and CD

Table 14: Replaceable Part

Part number	Description
116-1002-00	YOPM PCMCIA card

