


CMA5000 CD-OTDR SPECIFICATIONS

OTDR/Chromatic Dispersion Application



The field portable CMA5000 OTDR/ Chromatic Dispersion (OTDR/CD) measurement system is a dedicated module that combines the advanced capabilities of Anritsu’s OTDR technology with Anritsu’s experience in Chromatic Dispersion. The CMA5000 OTDR/CD measurement system gives installers and network providers a combined module that can be used as an OTDR and a chromatic dispersion measurement system, reducing testing times while increasing network performance. The CMA5000 OTDR/CD measurement system is based upon the industry accepted time-of-flight measurement method (FOTP-168) that can evaluate chromatic dispersion of individual fiber links. Utilizing a single fiber for the test and multiple wavelengths results in an increase in the accuracy of the measurement, as well as a reduction in the testing time. This translates into improved network performance and efficiency, resulting in increased revenue for the network provider.

Chromatic Dispersion Specifications

Anritsu understands how valuable your time is, so we’ve provided intuitive, easy-to-use setup menus and single-button operation. The CMA5000 OTDR/CD measurement system has been designed to provide optimal test efficiency to facilitate quicker turn-up of services and reduce the cost of testing. The combined unit has an auto-test feature that will determine the optimum settings. In addition, intuitive setup menus guide the user through a few minor settings that minimize the testing and setup times. The field portable CMA5000 OTDR/CD is an accurate system available for measuring both Chromatic Dispersion, loss and attenuation on all single-mode fiber types providing installers, carriers and system providers increased revenue through optimized network bandwidth, while improving efficiency and reducing operational expenses through proper CD mitigation and compensation techniques.

Chromatic Dispersion Specifications	
Wavelength Range	1310 nm through 1625 nm
Dynamic Range	37 dB (100 km is the typical range when using all 6 wavelengths)
Dispersion Range	There is no physical limitation on either the negative or positive dispersion that can be measured.
Dispersion Accuracy *1	± 0.7 ps/nm*km or $\pm 4\%$ (greater number)
λ_0 Accuracy	Typically ± 10 nm
Number of Testing Wavelengths	6
Test Time	<4 minutes for 50 km
Number of Fibers Required	One

OTDR Module Specifications	
Fiber Type	Single-mode (Tri-wavelegth)
Center Wavelength	1310 nm ± 20 nm 1550 nm ± 20 nm 1625 nm ± 15 nm
Spectral Width (RMS)	1310 nm: <15 nm 1550 nm: <15 nm 1625 nm: <15 nm
Dynamic Range *2	1310 nm: 38 dB 1550 nm: 38 dB 1625 nm: 38 dB
Initial Reflective Deadzone *3	1310 nm: 4 meters 1550 nm: 4 meters 1625 nm: 4 meters
Initial Non-Reflective Deadzone *4	1310 nm: 9 meters 1550 nm: 8 meters 1625 nm: 9 meters
Linearity	0.04 dB/dB
Pulsewidth *5	5 ns to 20 μ s
Distance Resolution	0.0001 km, 0.1 m, 1 ft, 0.0001 mi
Distance Range Setting	5, 20, 50, 125, 250, 300 km
Loss Resolution	0.001 dB
Distance Sampling (Range Dependent)	0.125, 0.25, 0.5, 1, 2, 4, 8, 16 m
Data Points	Up to 256,000
Distance Accuracy	0.0025% of distance measurement \pm distance resolution \pm index uncertainty
Laser Safety	Meets IEC60825-1 Class I and CDRH Class 1 Requirements (Eye Safe) 21 CFR 1040

*1: C- and L- bands

*2: SNR=1 with up to 256k averages (typical, subtract approximately 2 dB of range to 98% peak noise. Bellcore TR-TSY-000196 Issue 2)

*3: Using Bellcore TR-TSY- 000196 Issue (typical)

*4: Deadzones measured on -45 dB reflections (typical)

*5: Wavelength dependent

Specifications are subject to change without notice

Anritsu Corporation

5-1-1 Onna, Atsugi-shi, Kanagawa, 243-8555
Japan
Phone: +81-46-223-1111
Fax: +81-46-296-1264

• U.S.A.**Anritsu Company**

1155 East Collins Blvd., Richardson, TX 75081,
U.S.A.
Toll Free: 1-800-ANRITSU (267-4878)
Phone: +1-972-644-1777
Fax: +1-972-671-1877

• Canada**Anritsu Electronics Ltd.**

700 Silver Seven Road, Suite 120, Kanata,
Ontario K2V 1C3, Canada
Phone: +1-613-591-2003
Fax: +1-613-591-1006

• Brazil**Anritsu Eletrônica Ltda.**

Praca Amadeu Amaral, 27 - 1 Andar
01327-010-Paraiso-São Paulo-Brazil
Phone: +55-11-3283-2511
Fax: +55-11-3288-6940

• U.K.**Anritsu EMEA Ltd.**

200 Capability Green, Luton, Bedfordshire LU1
3LU, U.K.
Phone: +44-1582-433280
Fax: +44-1582-731303

• France**Anritsu S.A.**

9, Avenue du Québec Z.A. de Courtabœuf
91951 Les Ulis Cedex, France
Phone: +33-1-60-92-15-50
Fax: +33-1-64-46-10-65

• Germany**Anritsu GmbH**

Nemetschek Haus, Konrad-Zuse-Platz 1
81829 München, Germany
Phone: +49 89 442308-0
Fax: +49 89 442308-55

• Italy**Anritsu S.p.A.**

Via Elio Vittorini, 129, 00144 Roma, Italy
Phone: +39-6-509-9711
Fax: +39-6-502-2425

• Sweden**Anritsu AB**

Borgafjordsgatan 13, 164 40 KISTA, Sweden
Phone: +46-853470700
Fax: +46-853470730

• Finland**Anritsu AB**

Teknobulevardi 3-5, FI-01530 Vantaa, Finland
Phone: +358-20-741-8100
Fax: +358-20-741-8111

• Denmark**Anritsu A/S**

Kirkebjerg Allé 90 DK-2605 Brøndby, Denmark
Phone: +45-72112200
Fax: +45-72112210

• Spain**Anritsu EMEA Ltd.****Oficina de Representación en España**

Edificio Veganova
Avda de la Vega, n° 1 (edf 8, pl 1, of 8)
28108 ALCOBENDAS - Madrid, Spain
Phone: +34-914905761
Fax: +34-914905762

• United Arab Emirates**Anritsu EMEA Ltd.****Dubai Liaison Office**

P O Box 500413 - Dubai Internet City
Al Thuraya Building, Tower 1, Suit 701, 7th
Floor
Dubai, United Arab Emirates
Phone: +971-4-3670352
Fax: +971-4-3688460

• Singapore**Anritsu Pte Ltd.**

10, Hoe Chiang Road, #07-01/02, Keppel
Towers,
Singapore 089315
Phone: +65-6282-2400
Fax: +65-6282-2533

• P.R. China (Hong Kong)**Anritsu Company Ltd.**

Suite 923, 9/F., Chinachem Golden Plaza, 77
Mody Road,
Tsimshatsui East, Kowloon, Hong Kong, P.R.
China
Phone: +852-2301-4980
Fax: +852-2301-3545

• P.R. China (Beijing)**Anritsu Company Ltd.****Beijing Representative Office**

Room 1515, Beijing Fortune Building,
No. 5, Dong-San-Huan Bei Road,
Chao-Yang District, Beijing 10004, P.R. China
Phone: +86-10-6590-9230
Fax: +86-10-6590-9235

• Korea**Anritsu Corporation, Ltd.**

8F Hyunjuk Building, 832-41, Yeoksam dong,
Kangnam-ku, Seoul, 135-080, Korea
Phone: +82-2-553-6603
Fax: +82-2-553-6604

• Australia**Anritsu Pty Ltd.**

Unit 21 / 270 Ferntree Gully Road,
Notting Hill, Victoria 3168 Australia
Phone: +61-3-9558-8177
Fax: +61-3-9558-8255

• Taiwan**Anritsu Company Inc.**

7F, No. 316, Sec. 1, Neihu Rd., Taipei 114,
Taiwan
Phone: +886-2-8751-1816
Fax: +886-2-8751-1817

• India**Anritsu Corporation****India Liaison Office**

Unit No. S-3, Second Floor, Esteem Red Cross
Bhavan,
No. 26, Race Course Road, Bangalore 560
001, India
Phone: +91-80-32944707
Fax: +91-80-22356648