
1100

DOP POLARIZATION-OTDR

POTDR-1100

NETWORK TESTING



PMD is a major obstacle to high-quality, high-bit-rate transmission. Despite better singlemode fiber production techniques that considerably reduce PMD, at times it is more economical to upgrade fiber links rather than replace them. So, when upgrading old fiber links to higher bit-rate, working with a mix of newer and older fibers means you can encounter huge PMD variations in a given link span.

Locating Potential Trouble Spots

That's why network operators are looking for ways to locate high-PMD link spans, in order to replace old fibers when upgrading their systems. Together with its Swiss partner, GAP OPTIQUE, EXFO is introducing a new test method, using a DOP-based polarization optical time domain reflectometer (P-OTDR), to meet that specific need.

You'll find the leading-edge technology of the POTDR-1100 DOP Polarization-OTDR packaged conveniently in a four-slot module for EXFO's proven FTB-400 Universal Test System.



SPECIFICATIONS¹

P-OTDR*				
Wavelength		Fixed wavelength DFB laser in C+L-band		
Selectable pulse widths (ns)		30, 100, 275, 500		
Selectable ranges (km)		2.5, 5, 10, 20, 40, 80, 120		
Dynamic range		20 dB typical (500 ns pulse)		
Available measurements		Standard OTDR traces		
		Stokes parameters: s1, s2 and s3		
		Degree of Polarization (DOP)		
*All specifications are for a 9	9-minute measuren	nent time.		
PMD DETECTION*				
Detection range ²		> 12 dB		
Spatial resolution ³		500 m		
Detection efficiency ⁴		typical > 80 % for PMD > 1 ps/sqrt (km)		
*All specifications are for a 2	275 ns pulse with a	a 9-minute measurement time.		
INTERFACES				
Optical interface		EUI-28/89/91/95 with APC		
User interface		Windows®-based application		
GENERAL SPECIFICATION	S*			
Power supply		100-240 VAC, 50/60 Hz and 12-20 VDC		
Temperature	Operating	10 °C to 35 °C		
	Storage	-40 °C to 60 °C		
Weight	Ţ.	8 kg		
Dimensions (W x H x D)		33.65 cm x 28.57 cm x 17.14 cm (with FTB-400)		
*Also refer to EXFO FTB-40	0 Universal Test S	ystem specifications.		
LASER SAFETY				
21 CFR-1040.10				
IEC-60825-1 am.2 :2001	CLASS 1 LASER PRODUCT			


Notes

- Not applicable on spooled fibers. Applicable to fibers on drums with a minimum diamter of 1 m.

 Detection range can be increased by using longer pulses (500 ns), but the PMD detection efficiency will be degraded.

 Spatial resolution indicates the granularity of the information provided by the high-PMD detection algorithm. A more precise location of the beginning and end of the high-PMD section is usually possible by zooming in on the OTDR trace.

 The detection technique is based on the detection of poor mode coupling along a fiber link. It works well for "UNSPUN" standard singlemode fibers that exhibit high-PMD. Recent fibers that were spunned during their fabrication process usually have PMD below the sensitivity of the instrument. If a spunned fiber has a high-PMD it cannot be tested with the instrument (unpredictable results).





Rugged Handheld Solutions

- OLTS
- -Power meter -Light source
- -Talk set



Optical Fiber

OTDR OLTS

- ORL meter -Switch
 - Multiwavelength meter

- -OSA
- PMD analyzer - Chromatic dispersion analyzer

- 10/100 and Gigabit Ethernet
- SONET/SDH (DS0 to OC-192c) -SDH/PDH (64 kb/s to STM-64c)

Corporate Headquarters > 400 Godin Avenue, Vanier (Quebec) G1M 2K2 CANADA | Tel.: 1 418 683-0211 | Fax: 1 418 683-2170 | info@exfo.com

		Toll	-free: 1 800 663-3936 (USA	and Canada) www.exfo.com
EXFO America	4275 Kellway Circle, Suite 122	Addison, TX 75001 USA	Tel.: 1 800 663-3936	Fax: 1 972 836-0164
EXFO Europe	Le Dynasteur, 10/12 rue Andras Beck	92366 Meudon la Forêt Cedex FRANCE	Tel.: +33.1.40.83.85.85	Fax: +33.1.40.83.04.42
EXFO Asia-Pacific	151 Chin Swee Road, #03-29 Manhattan House	SINGAPORE 169876	Tel.: +65 6333 8241	Fax: +65 6333 8242
EXFO China	Beijing New Century Hotel Office Tower, Room 1754-1755	Beijing 100044 P. R. CHINA	Tel.: +86 (10) 6849 2738	Fax: +86 (10) 6849 2662
	No. 6 Southern Capital Gym Road			

EXFO is certified ISO 9001 and attests to the quality of these products. This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. EXFO has made every effort to ensure that the information contained in this specification sheet is accurate. However, we accept no responsibility for any errors or omissions, and we reserve the right to modify design, characteristics and products at any time without obligation. Units of measurement in this document conform to SI standards and practices.

Contact EXFO for prices and availability or to obtain the phone number of your local EXFO distributor.

For the most recent version of this spec sheet, please go to the EXFO website at http://www.exfo.com/specs

In case of discrepancy, the Web version takes precedence over any printed literature.





